
SwiftSensors



Wireless Medical Grade Temperature Sensor - 104

Part Number: SS3-104

Overview

Swift Sensors Wireless Medical Grade Temperature Sensor includes a 1m NTC temperature probe with a medical grade termination and can measure temperatures between -0°C to +50°C (32°F to +122°F). This sensor is ideal for medical buildings and for analyzing precise measurements in critical environments. Users can set the inspection rate and thresholds for notifications via SMS text, email, and phone call.

Simple, Plug-and-Play Deployment

Place the small battery-powered sensor in the location or on the equipment you need to monitor. The Swift Sensors Gateway instantly identifies the sensor and establishes secure communication. No wires to connect. No software to Install.

Sensors are powered with 2 AAA lithium polymer batteries with an average lifespan of 6 - 8 years. Sensors can be powered on or put into sleep mode by pressingthe center of the sensor. A green LED in the sensor blinks when the sensor powers on, turns solid when transitioning to sleep mode, and will blink when the "Find my Sensor" command is sent from the Console. All sensors send encrypted data to the gateway.

Secure, Scalable, Cloud Architecture

The system is 100% cloud-managed. The gateway securely transmits sensor data to the Swift Sensors Cloud using 256-bit AES encryption. The system is scalable from a single sensor, one site application to multi-site enterprises with thousands of sensors.

Real-time Monitoring and Analytics with Actionable Data

Swift Sensors Console allows real-time asset monitoring and sophisticated analysis from anywhere – on a computer, tablet, or smartphone. Data analytics provide operational insights and deep visibility. SMS text, email, and phone call notifications can be set based on customizable threshold values and complex rules by individual sensors or sensor groups.



Operational Specifications:	
Power	1.8 - 3.6VDC, 0.05mW Average
Battery Type	AAA x2 Replaceable "L92" Lithium Polymer
Operating Voltage	1.8VDC - 3.6VDC
Avg. Current Consumption	16uA (Active), 500uA (Command ACK), <5uA(Sleep)
Operating Temperature	-40°C to +60°C (-40°F to +140°F) Defined by Batteries
Operating Environment	Indoor/Outdoor, 0-95%+ RH
Battery Life (Average)	6 - 8 Years
Communication Protocol	BLE/BT5 2.4Ghz
BLE Chipset	nRF52840
TX Strength	Default +8dBm
Range	70m - 90m (250ft - 300ft) Line-of-Sight
	30m - 45m (100ft - 150ft) Non Line-of-Sight
Encryption	128-Bit AES Encryption
Button Press	Click to turn on. Press and Hold 2 sec to put in sleep mode
LED	Green LED: 2 sec. blinking when turning on
	Green LED: 2 sec. solid when entering sleep mode
Find My Sensor	Command from Console to blink sensor LED
Weight	56g (2 oz)
Dimensions	77.5mm x 57.5mm x 44mm (2.26in. x 1.73in. x 0.73in.)
Enclosure Material	ABS PA-765+
IP Rating	IP66
Probe Dimensions	610mm Probe Length
	Insulated 30awg Wire, <2mm Cable Diameter
	9.53mm / 0.375" Insulated Disc Capsule
	FCC ID: X8WBT840F
	IC ID: 4100A-BT840F
CE VROHS	CE Compliance: 2014/35/EU, 2014/53/EU, 2014/30/EU



Operational Specifications Cont.:	
EMC Compliance	FCC Part 15 Class B
Flammability Rating	UL94-0V
Warranty	2-years

Measurements Specs:	Temperature (C)
Measurement Range	0°C to +50°C (32°F to +122°F)
Accuracy	0.1°C
Precision	0.01°C
Inspection Rate	1 - 30 Minutes, 5-Minute Default

Swift Sensors Gateway

The Swift Sensors Gateway collects encrypted data from sensors located within the specified communication range (< 90m/300ft) and then transmits the sensor data to the Swift Sensors Cloud through either Ethernet, Wi-Fi, or cellular. The gateway auto-detects all sensors within range and will immediately establish secure communication without any user configuration or setup. Each gateway can support up to 150 Series 3 sensors.

Swift Sensors Console

All sensor data is logged and stored in the Swift Sensors Cloud. The Swift Sensors Console is configured to monitor and track all sensor data in the cloud. Multiple thresholds and alerts can be set separately for each sensor to supply notification via SMS text, email, or phone call. The console can be viewed in a web browser on a computer, tablet, or smartphone.

No programming is required to configure the console. An API to the Swift Sensors Platform allows integration with other data sources and 3rd-party data analytics tools.